




Model	Color	Current	Power	Mode
OPT-CFLG156100-UV	Ultraviolet (365nm)	20A	480W	Strobe
OPT-CFLG156100-UV	Ultraviolet (365nm)	9.4A	225.6W	Continuous
OPT-CFLG156100-UV	Ultraviolet (385nm)	20A	480W	Strobe
OPT-CFLG156100-UV	Ultraviolet (385nm)	9.4A	225.6W	Continuous
OPT-CFLG156100-UV	Ultraviolet (405nm)	20A	480W	Strobe
OPT-CFLG156100-UV	Ultraviolet (405nm)	9.4A	225.6W	Continuous

WS 28K7Z, M30x1.0, 7 Pin
or Compactible Connector





Pin	Pin Definition
1	Light +
2	Light -
3	Fan +
4	Fan -
5	NC*
6	NC*
7	NC

* DO NOT CONNECT ANY COMPONENT



12 x M4 ∇ 4
Another 6 in the opposite



Copyright © 2011 by OPT All Rights Reserved		View Angle		Standard Difference	IT14	Remark 1.stroboscopic working: Maximum pulse width 30s, duty ratio 50%; 2.continuous working: The controller gear 120; 3.Light source using with 3 meters extension cords. 4.Advised Controller: OPT-DPA20024E	 OPT[®] MACHINE VISION	
		Paper Size	A4	Scale	1:2		OPT-CFLG156100-UV	
Drawing Code	KFBZ20190520KF0701	Drawing Date	2017/5/22	Revised Date	2019/6/9	Version		V1.0