



Model	Color	Current	Power	Mode	Channel
OPT-CFLG15658-UV	Ultraviolet (365nm)	10A	240W	Strobe	2
OPT-CFLG15658-UV	Ultraviolet (365nm)	4.7A	112.8W	Continuous	2
OPT-CFLG15658-UV	Ultraviolet (385nm)	10A	240W	Strobe	2
OPT-CFLG15658-UV	Ultraviolet (385nm)	4.7A	112.8W	Continuous	2
OPT-CFLG15658-UV	Ultraviolet (405nm)	10A	240W	Strobe	2
OPT-CFLG15658-UV	Ultraviolet (405nm)	4.7A	112.8W	Continuous	2



ZQ GX16M-6A, M16x1.0, 6 Pin or Compactible Connector		Pin	Pin Definition
		1	Light +
		2	Light -
		3	Fan +
		4	Fan -
		5	NC*
		6	NC*
* DO NOT CONNECT ANY COMPONENT			



View Angle		Standard Difference		Remark	
		IT14		1.stroboscopic working: Maximum pulse width 30s, duty ratio 50%; 2.continuous working: The controller gear 120; 3.Advised Controller: OPT-APA6024 OPT-DPA6024	
Paper Size		Scale		Version	
A ₄		1:2		V1.0	

Copyright © 2011 by OPT
All Rights Reserved

Drawing Code KFBZ20190520KF0701

Drawing Date 2017/5/22 Revised Date 2019/6/4

 **OPT MACHINE VISION**

OPT-CFLG15658-UV